



Data Sheet: Cleaning Strategy
Document Title: CSO&M Data Sheet
Document Number: 001
Document Issue Date: Sept 11

Kwik-klik

FAST FIT TEMPORARY HOARDING SYSTEMS

ecogenik™

100% recycled hoarding panels

NOTES

Cleaning Strategy & Maintenance Data Sheet for all Kwik-Klik, Hygienik and Ecogenik products.

Hygienik, Kwik-Klik and Ecogenik Limited Cleaning Systems

Hygienik and Kwik-Klik products can be readily cleaned by regularly washing with copious quantities of water or diluted soap/detergent solutions. The latter having the added advantage of making the PVC surface temporarily anti-static.

We also supply multi-purpose cleaning wipes that are quick, convenient and highly effective for Hygienik and Kwik-Klik products that remove silicone PU Foam, most adhesives, paints, oils and grease from your hands, tools and surfaces. Supplied in containers of 80 wipes, 20cm x 30cm.

Proprietary cleaners should not be used unless specifically stated to be suitable for the materials, as they contain an abrasive or a solvent that could adversely affect the PVC surface. Whilst the recommended maximum continuous working temperature of Hygienik and Kwik-Klik products is 60 deg/140 Farenheight, the material may be pressure cleaned for sterilisation purposes.

© Copyright 2011 Kwik-Klik Hoardings Ltd
Kwik-Klik Hoardings Ltd, Unit 3a, A1 Business Park,
370 Bradford Road, Brighouse, West Yorkshire, HD6 4DJ

For Further Technical Advice:
Telephone: 01484 717192
Email: tony@kwik-klik.co.uk
www.kwik-klik.co.uk www.ecogenik.co.uk

© Copyright 2011 Hygienik Systems Ltd
Hygienik Systems Ltd, Unit 3a, A1 Business Park,
370 Bradford Road, Brighouse, West Yorkshire, HD6 4DJ

For Further Technical Advice:
Telephone: 01274 355777
Email: matt@hygienee.com
www.hygienee.com